END OF TRIP

Specifications
CONSTRUCTION
CabinetHeavy gauge steelFront glassDouble pane
FINISH
Custom designed vinyl overlay
POWER OPTIONS
Standard 240v 10a GPO
DIMENSIONS
Width 990mm Height 1830mm Depth 930mm

Details

- · Custom branded to your requirements
- Custom product range (49 products available) to suit all end of trip users and proven popular across our national network 70% of products are custom designed and packaged for this service and exclusive to all4cycling
- 100% cash-free with card payments only
- Machine maintenance/servicing and restocking by all4cycling
- Remote monitoring ensures replenishment when required
- · Sales reporting included at end of month
- Sensit[®] patented guaranteed delivery system
- State-of-the-art electronics
- EnergySensit[®] cost-saver

Cleaning Instructions

Wipe with a damp cloth for surface cleaning. Regular cleaning may be done with a solution of warm water and a non-abrasive pH neutral detergent solution. Surfaces should be thoroughly rinsed after cleaning to remove all residue. Regular glass cleaner for cabinet glass. All4cycling will use a hospital grade sanitizer to wipe down all touch points at each replenish, but we do recommend that you also do this.



All4cycling PTY Ltd Factory C2, 2A Westall Road Clayton VIC Australia 3168 Email: info@all4cycling.com.au Phone: 1300 429 254 Website: all4cycling.com.au